

K7 Splice Cassette 1 Slot, Uni Zone-4 + 2 PLC 7x4 mm

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Part Number:
N541248A

The type of splice technology used (fusion or mechanical) and whether planar light circuit (PLC) splitters are required will help determine which BPEO splice tray should be selected.

- Compact trays are 5 mm in height and occupy one slot in the fiber organizer.
- Standard trays are 10 mm in height and occupy two slots.
- All BPEO splice trays accept heat-shrink fusion splice protectors of 2.4 mm x 45 mm or 2.4 mm x 60 mm (after shrinkage). For example, Fiber Closure BPEO size 1 is equipped with a 12-slot fiber organizer. If using a 5 mm tray for 12 fusion splices, the total capacity of the closure will be 144 splices.

K7 Splice Cassette 1 Slot, Uni Zone-4 + 2 PLC 7x4 mm



Specifications

General Specifications	
Brand	BPEO
Product Type	Splice Trays
Standards	
Fiber Standards	G.652 / G.657
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Design	
Splice Tray Type	K7 Splice Tray
Number of Splice Trays	1
Color	Light basic, RAL 7035
Splice Protectors Type	Heat Shrink, single fiber
Splice Tray Capacity Mass Fusion	0
Splice Tray Capacity Single Fiber	4
Number of Splice Protectors	4
Dimensions	
Height	5 mm (0.2 in)
Ordering Information	
Product Number	N541248A
Packaging Method	Box
Module Capacity	0
Package Contents	20
Units per Delivery	20/1

K7 Splice Cassette 1 Slot, Uni Zone-4 + 2 PLC 7x4 mm

The Corning logo is a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.