

Splice Closure Fiber (SCF) 6-in diameter, 22-in dome length, 4 drop ports, 0.4-in tray height stacker, reduced slack storage



Part Number:
SCF-6C22-02-F

Corning Splice Closure (SCF) with Mechanical End Cap is designed for splicing fibers in aerial, duct, and buried applications. These sealed canister closures are available in configurations that can accommodate from 72 to 576 single-fiber splices, or from a 288- to 1296-fiber capacity if splicing ribbons.

The consolidation of multipoint tails for up to 24 flat cables is accomplished with optional add-a-cable kits. Designed for configuration flexibility, these closures offer expanded slack storage, various tray heights, and mass-platform storage.

Features and Benefits

Sealed butt-style closure

Environmental protection

Modular fiber management system

Preserve the ease of traditional (flat) ribbon splicing while gaining simplified ribbon fiber routing

Increased splicing capability in the field

Aerial, wall, pole, direct

Suitable for all applications

Environmental protection

Splice Closure Fiber (SCF) 6-in diameter, 22-in dome length, 4 drop ports, 0.4-in tray height stacker, reduced slack storage



Specifications

General Specifications	
Application	CATV Environments, Carrier Networks
Mounting Type	Buried, Pole-mount, Strand-mount, Wall-Mountable

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Closure Shape	Dome
Closure Type	Butt
Distribution Port Count	4
Main cable circular port count	2
Main Cable Diameter	12-22mm
Main cable range	12 mm to 22 mm (0.47 in to 0.87 in)
Max number of trays	8
Maximum splice fiber capacity	192 Single Fiber / 288 Ribbon Fiber
Maximum tray count	8
Number of Cable Entries	6
Number of Distribution/Drop Cables ports	4
Number of Ports	4
SCF Type	8 in canister, 28 in LID

Dimensions	
Height	58.4 cm
Width	17.8 cm

Splice Closure Fiber (SCF) 6-in diameter, 22-in dome length, 4 drop ports, 0.4-in tray height stacker, reduced slack storage



Ordering Information	
Product Number	SCF-6C22-02-F
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.