

# EDGE™ Housing 1 Rack Unit, White

CORNING

**Part Number:  
EDGE-01U-FL**

EDGE™ housings are high-density, preterminated fibre optic hardware solutions. They offer industry-leading connector density and easy finger/toolless access to enable faster moves, adds, and changes (MACs). The units can be configured to accommodate 96, 144, 288, or 576 fibers.

EDGE housings can be rack- or cabinet-mounted and are ideal for data centers, local area network (LAN) and storage area network (SAN) applications, as well as enterprise networks.



# EDGE™ Housing 1 Rack Unit, White



## Specifications

### General Specifications

Product Type	Housings
Environment	Indoor
Access Type	Front and rear access slidable
Mounting Type	Rack-mount, Cabinet-mount
Application	Data Center, Enterprise Networks

### Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

### Design

Lockable	Yes
Fiber Count	96
Number of Modules	8
Cable Entry Direction	Rear
Housing Type	EDGE
Number of Panels per Housing	8
Color	White
Fiber Capacity	96
Lock Position	Rear

### Dimensions

Height	44 mm (1.73 in)
Width	432 mm (17.01 in)
Depth	561 mm (22.09 in)

# EDGE™ Housing 1 Rack Unit, White

The CORNING logo is displayed in white, uppercase letters on a dark blue rectangular background.

## Ordering Information

Product Number	EDGE-01U-FL
Height Unit	1 U
Shipping Height	171 mm (6.73 in)
Shipping Width	565 mm (22.24 in)
Shipping Depth	657 mm (25.87 in)



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.