

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Universal Polarity



Part Number:
ETM-5B-G

EDGE™ Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets.


Features and Benefits

Designed for Duplex based infrastructure solutions


Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Universal Polarity



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Universal Polarity

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Universal Polarity



Specifications

| General Specifications | |
|------------------------|---------------------|
| Product Type | Modules |
| Fiber Category | Single-mode (OS2) |
| Application | Data Center LAN/SAN |

| Standards | |
|-----------|---|
| RoHS | Free of hazardous substances according to RoHS 2011/65/EU |

| Design | |
|------------------------------|--------------|
| Fiber Count | 12 |
| Adapter Type Back | MTP® |
| Adapter Color Back | Black / Red |
| Adapter Color Front | Blue |
| Adapter Type Front | Shuttered LC |
| Housing Type | Modules |
| Color | Grey |
| Number of Ports | 12 |
| Number of Adapters per Panel | 6 |

| Cable Design | |
|--------------|-----------|
| Polarity | Universal |

| Optical Specification - Hardware | |
|----------------------------------|--------------------------|
| Split Ratio Live/Tap | 50/50 |
| Splitter Loss for Tap Modules | 3.6 dB LIVE / 3.6 dB TAP |
| Fiber Category | Single-mode (OS2) |

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Universal Polarity



Connector Specs

| | |
|----------------|----|
| Connector Type | LC |
|----------------|----|

Specifications - Connector A

| | |
|------------------|-----------|
| Connector Type | LC Duplex |
| Ferrule Material | Ceramic |

Specifications - Connector B

| | |
|------------------|---------------|
| Connector Type | MTP® (pinned) |
| Ferrule Material | Ceramic |

Dimensions

| | |
|--------|-----------------|
| Height | 12 mm (0.47 in) |
| Width | 90 mm (3.54 in) |
| Depth | 165 mm (6.5 in) |
| Length | 0 mm (0 in) |

Ordering Information

| | |
|--------------------|---------------|
| Product Number | ETM-5B-G |
| EAN Code | 4056418149936 |
| Units per Delivery | 1/1 |



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm