

# K7 Splice Cassette 1 Slot, Bi Zone-12+12

The CORNING logo is displayed in white, uppercase letters on a dark blue rectangular background.

**Part Number:**  
**N541264A**

The type of splice technology used (fusion or mechanical) and whether planar light circuit (PLC) splitters are required will help determine which BPEO splice tray should be selected.

- Compact trays are 5 mm in height and occupy one slot in the fiber organiser.
- Standard trays are 10 mm in height and occupy two slots.
- All BPEO splice trays accept heat-shrink fusion splice protectors of 2.4 mm x 45 mm or 2.4 mm x 60 mm (after shrinkage). For example, fiber Closure BPEO size 1 is equipped with a 12-slot fiber organiser. If using a 5 mm tray for 12 fusion splices, the total capacity of the closure will be 144 splices.

# K7 Splice Cassette 1 Slot, Bi Zone-12+12

CORNING

## Specifications

### General Specifications

Brand	BPEO
Product Type	K7 Tray / Cassette

### Standards

Fiber Standards	ITU-G.657.A1
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

### Design

Splice Tray Type	Splice Trays
Splice Tray Category	Standard Bend Radius G652D
Number of Splice Trays	1
Splice Protectors Type	Heat Shrink, single fiber
Splice Tray Capacity Mass Fusion	0
Splice Tray Capacity Single Fiber	24
Number of Splice Protectors	24

### Dimensions

Height	5 mm (0.2 in)
Length	0 mm (0 in)

### Ordering Information

Product Number	N541264A
Package Contents	20
Packaging Method	Box
Module Capacity	0

# K7 Splice Cassette 1 Slot, Bi Zone-12+12



## Ordering Information

Units per Delivery

20/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)