

ALTOS® Gel-Free, Triple-Jacket, Double-Armored Cables, 12-216 Fibers 192 F, 62.5 µm multimode (OM1)

CORNING

Part Number:
192KU6-T4130D20

Corning ALTOS® gel-free triple-jacket, double-armored cables are rugged, armored cables designed for direct-buried installations. The loose tube design provides stable performance over a wide temperature range and is compatible with any telecommunications-grade optical fiber.

Features and Benefits

Three jacket layers and two steel tape armor layers

Provide superior rodent resistance for direct-buried applications

Flexible, craft-friendly buffer tubes

Facilitate easy routing in closures

Gel-free waterblocking technology


Craft-friendly cable preparation

Polyethylene jacket


Rugged, durable and easy to strip (while providing superior protection against UV radiation, fungus, abrasion and other environmental factors)

Exceeds the RDUP requirements for mid-span buffer tube slack storage

Provides flexibility for mid-span access applications



ALTOS® Loose Tube, Gel-Free, Triple-Jacket, Double-Armored Cable, 192 F, 62.5 µm multimode (OM1)



ALTOS® Loose Tube, Gel-Free, Triple-Jacket, Double-Armored Cable, 192 F, 62.5 µm multimode (OM1)

ALTOS® Gel-Free, Triple-Jacket, Double-Armored Cables, 12-216 Fibers 192 F, 62.5 µm multimode (OM1)

CORNING

Specifications

General Specifications

Installation Methods	Direct Buried
Cable Type	Loose Tube
Environment	Outdoor
Product Type	Steel Tape Armor
Fiber Category	62.5 µm MM (OM1)
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	USDA Rural Development Programs
Design and Test Criteria	ANSI/ICEA S-87-640

Environmental Conditions

Notes	Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.
Temperature Range, Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Central Element	Dielectric
Fiber Count	192
Number of Ripcords	5
Buffer Tube Color Coding, Layer 1	Blue, Orange, Green, Brown
Outer Jacket Color	Black

ALTOS® Gel-Free, Triple-Jacket, Double-Armored Cables, 12-216 Fibers 192 F, 62.5 µm multimode (OM1)

CORNING

Cable Design

Outer Jacket Material	Polyethylene (PE)
Buffer Tube Diameter	2.5 mm (0.1 in)
Inner Jacket Material	Polyethylene (PE)
Intermediate Jacket Material	Polyethylene (PE)
Number of Active Tubes	16
Number of Filling Elements	2
Number of Tube Positions	18
Tape	Water-swellaable
Tape, Layer 2	Water-swellaable
Tape, Layer 3	Water-swellaable
Tape, Layer 4	Water-swellaable
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Color Code Standards	Telcordia

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Nominal Outer Diameter	24 mm (0.94 in)
Min. Bend Diameter Installation	720 mm (28.35 in)
Min. Bend Diameter Operation	480 mm (18.9 in)

Optical Characteristics

Fiber Code	K
Performance Option Code	30
Fiber Category	OM1
Fiber Type	Multimode
Fiber Name	62.5 µm MM (OM1)

ALTOS® Gel-Free, Triple-Jacket, Double-Armored Cables, 12-216 Fibers 192 F, 62.5 µm multimode (OM1)

CORNING

Optical Characteristics

Maximum Attenuation	3.4 dB/km / 1.0 dB/km
Wavelengths	850 nm / 1300 nm
Fiber Compliance	ISO/IEC 11801
Fiber Core Diameter	62.5 µm
Coating diameter	242 µm
Serial 1 Gigabit Ethernet	300 m / 550 m
Serial 10 Gigabit Ethernet	33 m / -
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 500 MHz*km

Dimensions

Cable Weight	473 kg/km (317.84 lb/1000 ft)
--------------	-------------------------------



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.