

ALTOS® Loose Tube, Gel-Free, Double-Jacket, Single-Armored Cable 60 F, 50 µm multimode (OM2)

CORNING

Part Number:
060TU5-T4131D20

ALTOS® gel-free, double-jacket, single-armored cables are rugged, armored cables designed for direct-buried installation while suitable for duct and aerial (lashed) installation. The loose tube design provides stable performance over a wide temperature range and is compatible with any telecommunications-grade optical fiber.

Features and Benefits

Gel-free waterblocking technology

Craft-friendly cable preparation

Corrugated steel tape armor

Provides rodent resistance for direct-buried applications

Flexible, craft-friendly buffer tubes

Facilitate easy routing in closures

SZ-stranded, loose tube design



Isolates fibers from installation and environmental rigors and facilitates mid-span access

Dielectric central strength member

No preferential bend and requires no bonding or grounding

Polyethylene jacket

Rugged, durable and easy to strip (while providing superior protection against UV radiation, fungus, abrasion and other environmental factors)



ALTOS® Loose Tube, Gel-Free, Double-Jacket, Single-Armored Cable 60 F, 50 µm multimode (OM2)

CORNING

Specifications

General Specifications

Installation Methods	Aerial, Direct Buried
Cable Type	Loose Tube
Environment	Outdoor
Product Type	Dielectric armor
Fiber Category	50 µm MM (OM2)
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	USDA Rural Development Programs
Design and Test Criteria	Telcordia GR-20, ICEA-640

Environmental Conditions

Notes	Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.
Temperature Range, Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Central Element	Dielectric
Fiber Count	60
Number of Ripcords	3
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)

ALTOS® Loose Tube, Gel-Free, Double-Jacket, Single-Armored Cable 60 F, 50 µm multimode (OM2)

CORNING

Cable Design

Tensile Strength Elements and/or Armoring - Layer 1	Corrugated steel tape armor
Buffer Tube Color	Blue, Orange, Green, Brown, Slate
Buffer Tube Diameter	2.5 mm (0.1 in)
Inner Jacket Material	Polyethylene (PE)
Number of Active Tubes	5
Number of Filling Elements	1
Number of Tube Positions	6
Tape	Water-swellaable
Tape, Layer 2	Water-swellaable
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Color Code Standards	Telcordia

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Nominal Outer Diameter	14.3 mm (0.56 in)
Min. Bend Diameter Installation	430 mm (16.93 in)
Min. Bend Diameter Operation	286 mm (11.26 in)

Optical Characteristics

Fiber Code	T
Performance Option Code	31
Fiber Category	OM2
Fiber Type	Multimode
Fiber Name	50 µm MM (OM2)
Maximum Attenuation	3.0 dB/km / 1.0 dB/km
Wavelengths	850 nm / 1300 nm

ALTOS® Loose Tube, Gel-Free, Double-Jacket, Single-Armored Cable 60 F, 50 µm multimode (OM2)

CORNING

Optical Characteristics

Fiber Compliance	IEC 60793-2-10
Fiber Core Diameter	50 µm
Serial 1 Gigabit Ethernet	750 m / 600 m
Serial 10 Gigabit Ethernet	150 m / -
Minimum Effective Modal Bandwidth (EMB)	950 MHz*km / -
Min. Overfilled Launch (OFL) Bandwidth	700 MHz*km / 500 MHz*km

Dimensions

Cable Weight	179 kg/km (120.28 lb/1000 ft)
--------------	-------------------------------



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.