

SST-UltraRibbon Single-Tube, Gel-Free, Armored Cable 288 F, Bend-improved Single-mode (OS2)

CORNING

Part Number:
288ZV5-14100D53

Corning SST-UltraRibbon gel-free cables continue the innovative breakthrough in outdoor cable technology by introducing a new generation of high-fiber-count gel-free cables. Providing high-fiber-counts in a rugged, compact design, the enhanced coupling features ensure the ribbon stack and cable act as one unit, providing long-term reliability in aerial, duct and direct-buried applications. These features also minimize ribbon movement in situations where cable vibration may occur. The cable consists of a single buffer tube containing 24-fiber and 36-fiber ribbons wrapped within a water-swellable foam tape and surrounded by a second water-swellable tape. Each 24-fiber and 36-fiber ribbon can be easily separated by hand into 12-fiber ribbons. Strength members located 180 degrees apart under the cable jacket provide tensile and anti-buckling strength. The cable is jacketed with a black UV-resistant polyethylene sheath.

Features and Benefits

Gel-free waterblocking technology

Craft-friendly cable preparation

Innovative waterblocking technology



Provides ribbon to cable coupling

Up to 432 fibers in a compact design

Easily fits in 1.25-in diameter inner duct

Each 12-fiber ribbon individually numbered

Easy identification



SST-UltraRibbon Single-Tube, Gel-Free, Armored Cable 288 F, Bend-improved Single-mode (OS2)

CORNING

Specifications

General Specifications

Installation Methods	Aerial, Duct
Cable Type	Ribbon
Product Type	Corrugated Steel Armor
Fiber Category	SMF-28® Ultra
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature Range, Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Buffer Tube Color	Natural
Fiber Count	288
Buffer Tube Diameter	14 mm (0.55 in)
Number of Ripcords	3
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)
Tensile Strength Elements and/or Armoring - Layer 1	Corrugated steel tape armor
Tensile Strength Elements and/or Armoring - Layer 2	Steel strength members
Tape	Waterblocking foam tape

SST-UltraRibbon Single-Tube, Gel-Free, Armored Cable 288 F, Bend-improved Single-mode (OS2)

CORNING

Cable Design

Tape, Layer 1	Water-swellable
Tape, Layer 2	Water-swellable
Ribbons per Tube	12
Fibers per Ribbon	24

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Nominal Outer Diameter	20.5 mm (0.81 in)
Min. Bend Diameter Operation	410 mm (16.14 in)
Min. Bend Diameter Installation	616 mm (24.25 in)

Optical Characteristics

Fiber Code	Z
Performance Option Code	00
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.35 dB/km / 0.35 dB/km / 0.25 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1

Dimensions

Cable Weight	375 kg/km (251.99 lb/1000 ft)
--------------	-------------------------------

SST-UltraRibbon Single-Tube, Gel-Free, Armored Cable 288 F, Bend-improved Single-mode (OS2)

The Corning logo consists of a solid blue square. Inside the square, the word "CORNING" is written in a white, serif, all-caps font, centered horizontally and vertically.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.