

MiniXtend® HD Cable with Binderless* FastAccess® Technology 144 F, SMF-28® Ultra 200 fiber, Single-mode (OS2)

CORNING

Part Number:
144ZH4-Y3F40A20

Corning® MiniXtend® HD Cables with Binderless* FastAccess® Technology are high-density micro cables that are up to 60 percent smaller and up to 70 percent lighter than standard loose tube cables and up to 20 percent smaller than standard micro cables.

The innovative Binderless FastAccess Technology improves cable handling and reduces access time up to 70 percent while lowering risk of cable and fiber damage. MiniXtend HD cables have an SZ-stranded loose tube construction and provide high fiber counts in limited duct space in long-haul, metro and access networks.

With a low-friction PE sheath, MiniXtend HD cables are optimized for blowing into microducts. Both the buffer tubes and the fibers contained within are color-coded for quick and easy identification.

MiniXtend HD cables feature Corning® SMF-28® Ultra 200 single-mode fiber (ITU-T G.652.D and ITU-T G.657. A1): the industry's first 200 micron fiber with a 9.2 micron mode-field diameter (MFD).

Features and Benefits

Binderless FastAccess® Technology

Innovative cable design that reduces cable access time up to 70 percent and lowers the risk of inadvertent fiber damage

Reduced outer cable diameter

High fiber density in microduct systems

Compact and light

CapEx-optimized installations and upgrades

Fully dielectric

No grounding required

Color-coded tubes and fibers

Easy identification of tubes and fibers



MiniXtend® HD Cable with Binderless* FastAccess® Technology, 144 F, SMF-28® Ultra 200 fiber, Single-mode (OS2)

MiniXtend® HD Cable with Binderless* FastAccess® Technology 144 F, SMF-28® Ultra 200 fiber, Single-mode (OS2)

CORNING

Specifications

General Specifications

Installation Methods	Microduct
Cable Type	Stranded Loose Tube
Environment	Outdoor
Product Type	Dielectric
Fiber Category	SMF-28® Ultra 200 Optical Fiber
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	A-DQ(ZN)2Y
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature Range, Installation	-15 °C to 60 °C (5 °F to 140 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Cable Marking	M#H#S#CORNING#Year# MINIXTEND(R) HD FAB CABLE 6x24 E9U200 LT1.7
Central Element	Dielectric
Fiber Count	144
Buffer Tube Color Coding, Layer 1	Blue, Orange, Green, Brown, Slate, White
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)
Outer Jacket Nominal Thickness	0.5 mm
Buffer Tube Diameter	1.7 mm

MiniXtend® HD Cable with Binderless* FastAccess® Technology 144 F, SMF-28® Ultra 200 fiber, Single-mode (OS2)

CORNING

Cable Design

Number of Active Tubes	6
Number of Tube Positions	6
Cable Marking Method	Laser printing
Fiber Coloring	1-12: blue, orange, green, brown, slate, white, red, black, yellow, violet, rose, aqua - 13-24: (all with one black ring mark) blue, orange, green, brown, slate, white, red, natural, yellow, violet, rose, aqua
Fibers per Tube	24
Color Code Standards	Telcordia

Mechanical Specifications

Crush Resistance (reversible), Outdoor Cable	1000 N/10 cm
Max. Tensile Strength, Short-Term	1000 N
Nominal Outer Diameter	6.3 mm
Min. Bend Diameter Installation	252 mm
Min. Bend Diameter Operation	190 mm
Min. Duct Size Diameter	8 mm
Optimal Duct Size	10 mm

Optical Characteristics

Fiber Code	Z
Performance Option Code	40
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 200 µm
Fiber Name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.34 dB/km / 0.34 dB/km / 0.20 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1
Cladding diameter	125 µm
Coating diameter	200 µm

MiniXtend® HD Cable with Binderless* FastAccess® Technology 144 F, SMF-28® Ultra 200 fiber, Single-mode (OS2)

CORNING

Optical Characteristics

Cable cutoff wavelength	1260 nm
Mode-Field Diameter at 1310 nm	9.2 µm

Dimensions

Cable Weight	36 kg/km
Max. cable length per reel/drum	12000 m

Ordering Information

Product Number	144ZH4-Y3F40A20
Maximum Delivery Length	12000 m



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.