


EDGE™ Preloaded Housings EDGE-02U with 24 Single-mode Modules

CORNING

Part Number:
EG02-UM0489G-24

Revolutionize your network infrastructure with our cutting-edge Preloaded Housing solution! Say goodbye to tedious manual module loading and embrace efficiency with our preloaded Edge™ and Edge8® housings. Experience seamless integration and rapid deployment, streamlining your operations while ensuring optimal performance. Plus, with an impressive 55% packaging weight reduction, you'll not only enjoy enhanced efficiency but also contribute to a greener, more sustainable future. Elevate your network capabilities with Corning's innovative solution, making the future of connectivity a reality today.



EDGE™ Preloaded Housings EDGE-02U with 24 Single-mode Modules

CORNING

Specifications

General Specifications

Product Type	Housings
Environment	Indoor
Fiber Category	Single-mode (OS2)
Access Type	Front and rear access slidable
Application	Data Center, Enterprise Networks
Brand	EDGE

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Lockable	Yes
Number of Modules	24
Cable entry type	Side brush entry
Number of Panels	24
Housing Color	Silver
Color	Silver
Panel or Module Type	EDGE
Fiber Capacity	288
Lock Position	Rear

Dimensions

Height	88 mm
Width	432 mm

EDGE™ Preloaded Housings EDGE-02U with 24 Single-mode Modules

CORNING

Ordering Information

Product Number	EG02-UM0489G-24
Package Contents	EDGE™ Housing 2U; Quick Start Guide, #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Velcro Strap, Fiber Optic Warning Label



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.