

# BPEO Fibre Closure Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre



**Part Number:**  
**B2-EDP-0000-000-30S-0000**

Fibre Closures BPEO are designed with flexibility in application in mind. Available in a range of sizes, they can be deployed above grade (pole, facade) or below grade (manhole, handhole). These closures can be used for fibre-to-the-home (FTTH) deployments and any type of optical fibre cable deployment in the outside plant. Mechanical and tool free: Easy to re-enter and close; integrated sealing gasket keeps water out. The built-in seals of the BPEO in conjunction with the latch mechanism ensure that the closure remains watertight even after frequent use. The sealing gasket requires no replacement and no addition of sealant material, even after several open/close operations.

## Features and Benefits

### Fibre organiser (ramp or flat)

Enables fibre and tube management, supports single fibre management

### Tool-less opening and closing

Quick-and-easy installation

### Use of ECAM: External Cable Assembly Module

Easy and fast addition of loop and drop cables, without disrupting already installed fiber and protecting the fiber organiser of any debris

### Integrated sealing gasket


Ensures water tightness and remains functional even after several open/close operations

### IP68 design


Reliable and watertight with an integrated valve for flash on-site testing

### No special tools required for opening and closing

Quick and easy, labor saving



BPEO Fibre Closure, Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre



BPEO Fibre Closure, Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre

# BPEO Fibre Closure Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre



BPEO Fibre Closure, Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre

## Specifications

General Specifications	
Installation Methods	Aerial, Manhole
Brand	BPEO
Environment	Outdoor
Mounting Type	Pole-mount, Strand mount, Wall-mount
Product type	Splice Closure
Branching	Yes

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature range, operation	-40 °C to 65 °C

# BPEO Fibre Closure Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre



Design	
Buffer storage	Installed
Closure shape	Canister
Closure type	Butt
Drop cable type	SST flat or round
Fibre Capacity	0
Fibre Type	For Bend Improved Fibre G.657
Input cable type	External cable assembly module (ECAM)
Main cable diameter	5-27 mm
Main cable oval port count	1
Max number of trays	30
Maximum splice fiber capacity	360/720
Number of Cable Entries	12
Number of distribution/drop cables ports	12
Number of ports - cut	1
Number of splice trays preloaded	30
Pigtail class	No Pigtail
Sealing type	Rubber Gasket
Splice tray capacity single fibre	12 to 24
Test valve	Included
Trays pre-installed	0
Number of single-fibre ports, SC APC connector	0
Number of pigtails	0

Ordering Information	
Product Number	B2-EDP-0000-000-30S-0000
Package contents	BPEO Closure equipped with a 30 High Density trays and transparent cover. All ports sealed with proper plugs. The anchoring brackets ( wall-mount or pole ), Cable Entries and Trays have to be ordered apart this closure.
Shipping Width	520 mm

# BPEO Fibre Closure Size 2 End Distribution Point for up to one express cable and up to 12 branch cables, pre-equipped with a 30 High Density Trays for up to 720 splices, for Low Bend Loss radius fibre



## Ordering Information

Units per delivery

1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany  
00 800 2676 4641 • FAX: • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.