

Everon® LAN1 Fibre Housing Front panel front panel loaded with LC Duplex Shuttered adapters (Breakout version), 12 Fibres, 1U, Multimode OM3/OM4, black



Part Number:
LAN1-12AD-ADPT-B

The Everon® LAN1 Fibre Housing family was designed for various applications in 19-racks and main distribution frames. The fixed or sliding housings can be equipped with industry common adapter types in different fibre categories and are suitable for direct field termination, fusion splicing with pigtails as well as preterminated solutions. The four back openings accommodate cable glands. Additional brackets for cable strain relief for FTTD/FTTO applications or U-Clips for Plug & Play™ and EDGE™ trunks can be mounted at the backside.

The space-optimized interior makes it easy to work with ongoing moves, adds and changes (MACs), thus reducing the risk of network disruptions.

Features and Benefits

Easy to remove top cover

No tools needed

Housing made of aluminium

Lightweight, but robust

Quick-mount feature

Allows single-person mounting of housing

Accomodate different termination methods

Pigtail splicing, field connectorisation, preterminated cables, Plug&Play™ or EDGE™ trunks can be installed in the same housing

Low installation depth

Mountable in shallow cabinets or racks

Multiple labelling options

Port numbering above and below adapter modules or customised labels



Everon® LAN1 Fibre Housing, Front panel front panel loaded with LC Duplex Shuttered adapters (Breakout version), 12 Fibres, 1U, Multimode OM3/OM4, black

Everon® LAN1 Fibre Housing Front panel front panel loaded with LC Duplex Shuttered adapters (Breakout version), 12 Fibres, 1U, Multimode OM3/OM4, black



Specifications

General Specifications	
Product type	Housings
Access type	Front, top, rear
Mounting Type	Rack-mount

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature range, installation	-10 °C to 60 °C
Temperature range, operation	-10 °C to 60 °C
Temperature range, storage	-10 °C to 60 °C

Design	
Lockable	No
Fibre count	12
Splice tray type	No Splice Trays
Housing material	Aluminum
Additional cable number reached w/accessories	4
Max. cable number in basic unit w/accessories	4
Cable entry type	Prepunched circular
Number of pigtails	0
Number of splice trays	0
Adapter colour front	Turquoise
Adapter type front	LC PC duplex shuttered
Splice protectors type	Without organizer and protectors
Number of adapters	6

Everon® LAN1 Fibre Housing Front panel front panel loaded with LC Duplex Shuttered adapters (Breakout version), 12 Fibres, 1U, Multimode OM3/OM4, black



Design	
Number of splice protectors	0
Total Splice Capacity	No Splice Trays

Design - Adapter	
Adapter housing colour	Black
Keyed adapter	No
Shuttered adapter	Yes
Adapter type	LC PC duplex shuttered

Specifications - Connector A	
Connector type	LC
Polish	PC

Specifications - Connector B	
Polish	PC

Dimensions	
Height	44 mm
Width	483 mm
Depth	233 mm

Ordering Information	
Product Number	LAN1-12AD-ADPT-B
Height Unit	1 U
Package contents	Everon LAN1 Fiber Housing with adapters, 1 x M20 cable gland and all accessories needed for the installation
Shipping Height	55 mm

Everon® LAN1 Fibre Housing Front panel front panel loaded with LC Duplex Shuttered adapters (Breakout version), 12 Fibres, 1U, Multimode OM3/OM4, black



Ordering Information	
Shipping Width	532 mm
Shipping Depth	350 mm
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.