

Pretium® Connector Housing (PCH) 2 rack unit, holds 4 CCHE Panels + MFT Tray holder with 4 MFT Trays capacity



CORNING

Part Number:
PCH-02U-SPL

The rack-mount Pretium® connector housings (PCH) are available in 1U, 2U and 4U sizes and mount in 19-in racks or cabinets. Combined with the modules, panels, harnesses, trunks and patch cords, they provide a tip-to-tip solution for your fiber optic network.

Features and Benefits

Compatible with Plug & Play™ Systems modules

Designed to support Plug & Play Systems applications

Splice in the housing

Saves rack space and the cost of the second housing

Removable top (1U, 2U)

Maximizes ease of access

Transparent front door (04U and 02U)

Permits viewing while protecting installed patch cords

Large removable fiber guides in front

Effectively manage high patch cord densities

Pretium® Connector Housing (PCH) 2 rack unit, holds 4 CCHE Panels + MFT Tray holder with 4 MFT Trays capacity



Specifications

| General Specifications | |
|------------------------|----------------------------------|
| Product type | Housings |
| Access type | Front access fixed |
| Mounting Type | Rack-mount |
| Application | Data Centre, Enterprise Networks |

| Standards | |
|-----------|---|
| RoHS | Free of hazardous substances according to RoHS 2011/65/EU |
| UL-Listed | United States and Canadian safety standards |

| Design | |
|------------------------------|---|
| Lockable | Yes |
| Splice tray type | Multifunction Tray |
| Cable entry type | Slotted |
| Housing type | PCH |
| Number of panels per housing | 4 |
| Panel or module type | CCH |
| Splice Tray Options | 6 category 2R, 2S, 2S long, 3 category 4R, 4S, 4S wide |
| Fibre Capacity | Up to 48 fibres installing FC/SC/ ST® compatible connectors, or up to 96 installing LC connectors |
| Lock Position | Front or rear |

| Design - Adapter | |
|------------------------|------|
| Adapter housing colour | Grey |

| Dimensions | |
|------------|-------|
| Height | 89 mm |

Pretium® Connector Housing (PCH) 2 rack unit, holds 4 CCHE Panels + MFT Tray holder with 4 MFT Trays capacity



| Dimensions | |
|------------|--------|
| Weight | 5.9 kg |

| Ordering Information | |
|----------------------|--|
| Product Number | PCH-02U-SPL |
| Height Unit | 2 U |
| Package contents | Housing; Installation Guide; 4 blank panels; unit ID label; 2 port identification labels for 2 panels; 3 #6-32 x .25 screws; 8 #10-32 x 50 screws; 4 #12-24 x 50 screws; 8 1/8 x 4-in tie wraps, white; spiral wrap, 2 ft; central member strain-relief clamp kit; bracket for mounting UCC clamp; universal cable clamp (UCC) kit with 5 cable inserts; double-sided hook and loop strap, 5/8-in; bracket to hold BTF kit; 2 #6-32, SS nylon self-locking hex nut |
| Shipping weight | 9.5 kg |
| Units per delivery | 1/1 |



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.