

Presslok™ Splice Connectors UCC, Jar



Part Number:
UCC-JAR

With the Presslok™ series of tools and connectors, service providers can meet the demand for enhanced customer services such as high-speed internet, video-on-demand, and video conferencing. Presslok connectors also offer full wire-range capability, increased port size to accommodate up to 2.08 mm (0.082 in) insulation sizes, and solvent resistant plastic construction. As new technologies migrate into the local loop, the importance of reliable connections in the embedded plant has increased exponentially. Each connection is a potential point of failure in high-bandwidth applications, which could require additional time and expense for a technician to repair. That is where the full line of Presslok connectors can really make a difference.

Features and Benefits

- Fast installation
- Ease of Use
- Wide Range of Common Wire Gauges
- Factory-installed sealant
- Dry versions available for Central Offices and Vaults



Presslok™ Splice Connectors UCC, Jar

CORNING

Specifications

General Specifications

Product type	Copper Splice Connector
--------------	-------------------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Composition	Gel-filled
No. of connections	Two (2)
Connector type	Cap
Conductor	AWG 26 - 22

Dimensions

Weight	0.5 kg
--------	--------

Ordering Information

Product Number	UCC-JAR
Packaging method	Jar
Units per delivery	5000/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.