

LC UPC duplex / LC UPC duplex, OS2 Bend-improved SM, 2 F, Zipcord , Flame Retardant Non Corrosive, 2.0 mm, 35 Meters

CORNING

Part Number:
040402G5Z20035M

Cable assemblies are an often overlooked, critical component of your inside plant connectivity portfolio. These products are the component that enables port replication and the ability to cost effectively transmit and receive services between the active electronics and end users. As the industry's leading supplier of cable assemblies, Corning's state-of-the-art manufacturing process ensures reliable connector performance with products that meet or exceed all industry standards for reflectance and insertion loss. Our ability to scale to meet your deployment needs is what sets us apart, along with the highest-quality fibre and factory-tested connectors. All assemblies undergo rigorous performance testing to ensure optimal quality in every connector. Constant process improvements offer a variety of options in fibre, cable, and connector types to meet your network's ever-evolving needs.

If you do not see what you are looking for here, please review the ordering matrix contained in the family specification sheet, or contact Customer Care at: Phone: +49 30 5303 2100 or Toll-free: 00 800 2676 4641.

Features and Benefits

State-Of-The-Art Manufacturing Processes

Corning proprietary manufacturing processes and advanced technology result in unsurpassed product consistency

Global operations


Worldwide manufacturing facilities and end-to-end vertical integration across the entire process ensure reliable supply and mitigate trade barriers or supply disruptions

Flexible design options

Choice of materials for strength elements and fibre properties dependent on application requirements

Superior Performance Testing

Every termination is tested to ensure the highest in network performance



LC UPC duplex / LC UPC duplex, OS2 Bend-improved SM, 2 F, Zipcord , Flame Retardant Non Corrosive, 2.0 mm, 35 Meters

CORNING

Specifications

Cable Material	
Fiber Count	2
Fiber Type	OS2 Bend-improved SM
Outer Diameter	2.0 mm
Flame Rating	Flame Retardant Non Corrosive
Aarmor	Non-armored
Length	35
Unit of Measure	Meters
Cable Type	Zipcord
Fiber Mode	Single-Mode

CONNECTOR_A_1 Material	
Connector	LC UPC duplex
Connector Keying	Non-Keyed
Connector Pairing	Duplex
Connector Loss	Standard Loss

CONNECTOR_B Material	
Connector	LC UPC duplex
Connector Pairing	Duplex
Connector Keying	Non-Keyed
Connector Loss	Standard Loss

Furcation A Material	
Outer Diameter	2.0 mm

LC UPC duplex / LC UPC duplex, OS2 Bend-improved SM, 2 F, Zipcord , Flame Retardant Non Corrosive, 2.0 mm, 35 Meters

CORNING

Furcation B Material

Outer Diameter	2.0 mm
----------------	--------



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.