

Everon® Copper Datacom Class I Patch Cord, 2xRJ45, Cat.8.1, S/FTP LSZH™ AWG 26 light grey, 2 m

CORNING

Part Number:
CCA HGB-M8002-A020-C0

The application-neutral Everon® Copper Datacom category 8.1 patch cords have four individual foil-shielded pairs (PiMF) and an additional braid shield (S/FTP). They are assembled with a shielded RJ45 connectors on each end. The zero halogen patch cords (LSZH™) are non-corrosive according to IEC 60754-2 (FRNC), low smoke according to IEC 61034 and flame retardant according to IEC 60332-1. Everon Copper Datacom CCAHGB patch cords provide additional latch protection. They are available in various lengths and colours.

Features and Benefits

Application-neutral due to using all four pairs of RJ45 connectors

Minimum surface transfer impedance of cable (<10 mΩ/m at 10 MHz)

Additional latch protection



Everon® Copper Datacom Class I Patch Cord, 2xRJ45, Cat.8.1, S/FTP LSZH™ AWG 26, light grey, 2 m

Everon® Copper Datacom Class I Patch Cord, 2xRJ45, Cat.8.1, S/FTP LSZH™ AWG 26 light grey, 2 m

CORNING

Specifications

General Specifications

Cable assembly type	Stranded patch cord
Environment	Indoor
Category	8.1
Cable type	S/FTP
Halogen-free	Yes
Brand	Everon

Standards

Flame retardance	Flame retardant according to IEC 60332-1-2 (single cable)
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Design And Test Criteria	Compliant with PoE / PoE++ IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt
Halogen content test	Low Smoke to IEC 61034
Level of corrosion	Non-corrosive according to IEC 60754-2

Environmental Conditions

Temperature range, installation	0 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Transport and indoor storage	Dry environment, no direct sunlight, room temperature ≤ 40 °C

Cable Design

Conductor insulation	Halogen-free foam-skin material
Twisting	2 cores to a pair
Pair screen	Al-laminated foil around each pair
Overall screen	Copper braid, tinned
Outer jacket material	LSZH/FRNC

Everon® Copper Datacom Class I Patch Cord, 2xRJ45, Cat.8.1, S/FTP LSZH™ AWG 26 light grey, 2 m

CORNING

Cable Design

Outer jacket colour	Light grey
---------------------	------------

Mechanical Specifications

Min. bend radius installation	47 mm
-------------------------------	-------

Specifications - Connector A

Connector type	RJ45 - 8/8
Durability Cycles	750 N/A
Connector Material	Pin gold plated 50µ inch

Specifications - Connector B

Connector type	RJ45 - 8/8
Durability Cycles	750 N/A
Connector Material	Pin gold plated 50µ inch

Electrical Specifications

Mutual capacity	1200 pF/km
Max. loop resistance	290 Ω/km
Insulation resistance	5000 MΩ*km
Impedance Zo at 1-100 MHz	100 Ω ± 5% at 100 MHz
Surface transfer impedance	10 N/A

Dimensions

Length	2 m
Weight	9 kg

Everon® Copper Datacom Class I Patch Cord, 2xRJ45, Cat.8.1, S/FTP LSZH™ AWG 26 light grey, 2 m

CORNING

Ordering Information

Product Number	CCA HGB-M8002-A020-C0
Packaging method	Corn Starch Bag
Shipping weight	0.1 kg
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.