

# UniCam® Connectors LC, Keyed, 50 um Multimode (OM3 OM4), Black

The CORNING logo is displayed in white, uppercase letters on a dark blue rectangular background.

**Part Number:**  
**95-05X-KB**

Corning® UniCam® connectors offer high optical performance in a fast, easy field-termination solution—ideal for fiber-to-the-workstation setups where time matters. Using precision mechanical splice tech, UniCam enables quick, cost-effective fiber installations. With the High-Performance Tool Kit, LC, SC, or ST® connectors install in just 50 seconds to one minute.

The lightweight tool and precision cleaver reduce human error, ensuring consistent terminations. The cleaver's dual-clamp design and the tool's go/no-go feedback confirm proper fiber mating. Installation is simple: strip, clean, cleave, cam, and crimp. Corning guarantees performance—if a connector doesn't meet specs, it's replaced.

UniCam connectors suit all field-installable fiber needs, reducing total cost. Each acts like a mini pigtail with a factory-installed fiber stub, aligned via patented splice tech. No epoxy or polishing needed.

For added security, Corning offers keyed LC connectors for up to eight segregated networks. Color-coded keys prevent unauthorized access and simplify ID. Keyed connectors on both patch panel sides ensure matched access rights—features not replicable with standard LC components.

# UniCam® Connectors LC, Keyed, 50 µm Multimode (OM3 OM4), Black



## Specifications

General Specifications	
Product Type	Field-Installable Connectors
Fiber Category	50 µm MM (OM3/OM4)
Corning Logo	Yes
Keyed (security)	Yes
Technology	No-Epoxy/No-Polish

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	Passed EIA/TIA 568-B.3

Environmental Conditions	
Temperature Range, Operation	-40 °C to 75 °C (-40 °F to 167 °F )

Design - Connector	
Connector Type	LC
Housing Color	Black
Boot Color	Black
Ferrule Material	Ceramic

Mechanical Specifications - Connector	
Nominal Fiber Outer Diameter	125 µm
Tensile Strength Jacketed Cable	50 N
Durability	≤ 0.2 dB change, 500 rematings, FOTP-21
Tensile Strength 900 µm Cable	4.9 N (1.1 lb) change ≤ 0.2 dB, FOTP-6

# UniCam® Connectors LC, Keyed, 50 um Multimode (OM3 OM4), Black



Optical Specifications - Connector	
Insertion Loss, Max.	0.75 dB
Reflectance	≤ -26 dB

Ordering Information	
Product Number	95-05X-KB
Packaging Method	Individual Pack
Package Contents	Keyed connector, trigger, crimp band, boot (900 μm), boot (3.0 mm), boot (2.0 mm)
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.