

Presslok™ Splice Connectors U1R, Box

CORNING

Part Number: U1R-BOX

With the Presslok™ series of tools and connectors, service providers can meet the demand for enhanced customer services such as high-speed internet, video-on-demand, and video conferencing. Presslok connectors also offer full wire-range capability, increased port size to accommodate up to 2.08 mm (0.082 in) insulation sizes, and solvent resistant plastic construction. As new technologies migrate into the local loop, the importance of reliable connections in the embedded plant has increased exponentially. Each connection is a potential point of failure in high-bandwidth applications, which could require additional time and expense for a technician to repair. That is where the full line of Presslok connectors can really make a difference.

Features and Benefits

Fast installation

Ease of Use

Wide Range of Common Wire Guages

Factory-installed sealant

Dry versions available for Central Offices and Vaults



Presslok™ Splice Connectors U1R, Box



Specifications

General Specifications

Product Type	Copper Splice Connector
--------------	-------------------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Composition	Gel-filled
No. of connections	Two (2)
Connector Type	Inline Drop
Conductor	24 - 19 AWG
Conductor Range	0.5 mm to 0.9 mm

Dimensions

Weight	0.08 kg
--------	---------

Ordering Information

Product Number	U1R-BOX
Packaging Method	Box
Units per Delivery	1000/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.