

EDGE8® MTP® to LC Duplex Module 8F, Bend-improved Single-mode (OS2), Ultra-Low-Loss

CORNING

Part Number:
ECM8-UM08-18-E8G-ULL

EDGE8® modules provide an interface between 8-fibre MTP®/MPO connectors and LC duplex connectors. Ultra-low-loss connectivity enables design flexibility to permit multiple potential connections within the system (e.g., 6-module link). These modules break out 8-fiber MTP terminations from the rear into 4x LC duplex connectivity at the front. The VFL-compatible shuttered adapters provide reliable dust protection without the need for dust caps and allow for easy fiber identification. All EDGE8 modules are manufactured with Corning® CleanAdvantage™ technology and an optimized MTP dust cap, eliminating the need for cleaning before initial field connection.

Features and Benefits

VFL-compatible shuttered LC adapters

Creates one-hand operation and decreases time needed to test and troubleshoot a link

Rear-loading capability

Decreases the time to prepare and install modules into fiber housings

High density


Module enables 576 fibers in a 4U housing and 144 fibers in a 1U

Low insertion loss performance

Improved performance specs allow for more mated pairs and/or longer link distances

Corning® CleanAdvantage™ technology and optimized dust cap

Eliminates the need for scoping and cleaning prior to initial field connection



EDGE8® MTP to LC Duplex Module, 8F, Bend-improved Single-mode (OS2), LC Duplex APC, Universal Polarity, Ultra-Low-Loss

EDGE8® MTP® to LC Duplex Module 8F, Bend-improved Single-mode (OS2), Ultra-Low-Loss

CORNING

Specifications

General Specifications

Product Type	Modules
Fiber Category	Bend-improved SM (OS2)
Application	Data Center

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Count	8
Adapter Type Back	MTP®
Adapter Color Back	Black
Adapter Color Front	Green
Adapter Type Front	Shuttered LC Duplex
Housing Type	EDGE
Panel or Module Type	EDGE8
Product Family	EDGE8

Cable Design

Polarity	Universal
----------	-----------

Optical Specification - Hardware

Module Insertion Loss, Max	0.6 dB
----------------------------	--------

Specifications - Connector A

Connector Type	MTP® (non-pinned)
----------------	-------------------

EDGE8® MTP® to LC Duplex Module 8F, Bend-improved Single-mode (OS2), Ultra-Low-Loss

CORNING

Specifications - Connector A

Polish	APC
Ferrule Material	Composite

Specifications - Connector B

Connector Type	LC duplex
Polish	APC
Ferrule Material	Ceramic

Dimensions

Width	121 mm
Depth	125 mm

Ordering Information

Product Number	ECM8-UM08-18-E8G-ULL
Packaging Method	Individual Blister Packs
Package Contents	Modules packaged in individual blister packs
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.