

No Polish Connectors Plus (NPC+) SC/OM3/4/250/900 (120 pieces)

CORNING

Part Number: NPCP-SC-OM34-120-C

The No Polish Connector Plus (NPC+™) is Corning's fastest and simplest field installable fiber connector, designed to deliver reliable optical performance with minimal tools and training. Featuring a factory polished end-face and a tool less mechanical splice design, NPC+ enables technicians to achieve consistent, high-quality terminations in seconds—without field polishing, fusion splicing, or proprietary installation tools. Engineered for speed, simplicity, and performance, NPC+ is ideal for drop repairs, restoration work, and on demand fiber terminations wherever an SC or LC connector footprint is required.

Features and Benefits

Installs in less than 10 seconds after cleaving fiber

Minimizes installation time and accelerates service turn-up

Tool-less connector activation

Uses only standard fiber preparation tools, reduces crew tooling cost and simplifies field deployment

Audible and tactile “click” feedback

Provides immediate confirmation of proper termination

Supports both 250 μm and 900 μm fibers

Enables use across a range of fiber and cable types

Single-reuse capability

Allows deactivation of the splice element and strain relief without additional tools



No Polish Connectors Plus (NPC+) SC/OM3/4/250/900 (120 pieces)



Specifications

General Specifications

Product Type	Field-Installable Connectors
Fiber Category	50 µm MM (OM3/OM4)
Technology	No-Epoxy/No-Polish

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	In compliance with environmental and mechanical requirements of TIA/ EIA-568-D.3, GR-1081, Issue 1 section 4.3 yield, Insertion loss requirements of GR-1081-CORE, Issue 1 (GR-326-CORE, Issue 4) Thermal Cycle and Thermal Age; Back reflection performance was typical of an index gel-matched mechanical splice connector, Back reflection performance was typical of an index gel-matched mechanical splice connector

Environmental Conditions

Temperature Range, Operation	-10 °C to 60 °C (14 °F to 140 °F)
Temperature Range, Storage	-40 °C to 85 °C (-40 °F to 185 °F)

Design - Connector

Connector Type	SC
Housing Color	Aqua
Ferrule Material	Yttria-stabilized Zirconia

Mechanical Specifications - Connector

Nominal Fiber Outer Diameter	125 µm
Durability	≤ 0.2 dB change, 500 rematings, FOTP-21

No Polish Connectors Plus (NPC+) SC/OM3/4/250/900 (120 pieces)



Optical Specifications - Connector

Polish	UPC
Insertion Loss, Max.	0.5 dB
Reflectance, Typical	< -30 dB

Dimensions

Weight	76 g
--------	------

Ordering Information

Product Number	NPCP-SC-OM34-120-C
Package Contents	120 piece box (6 connectors packaged in plastic thermoformed containers, 20 containers per box). One maintenance-free EasyCleaver. One semi-tight buffer clamp. Minimum Order Quantity: 120 PCE
Shipping Weight	886 g
Units per Delivery	120/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.