

MiniXtend® Cable with Binderless* FastAccess® Technology 72 F, SMF-28® Ultra fiber, Single-mode (G.652.D/G.657.A1)

CORNING

Part Number:
072ZM4-T4F22A20

Corning MiniXtend® Cable with Binderless* FastAccess® Technology is an all-dielectric loose tube cable designed for microduct applications and features industry-leading fiber density. The innovative Binderless FastAccess Technology improves cable handling and reduces access time up to 70 percent while lowering risk of cable and fiber damage. The MiniXtend Cable design reduces the cable diameter by up to 50 percent (versus traditional loose tube cables) which improves fiber density for duct applications and also enables new applications which can reduce total install cost by up to 60 percent.

*Corning's patented Binderless FastAccess Technology refers to the combination of a Corning FastAccess Technology jacket with an innovative technology used to bind cable construction through the manufacturing process, eliminating the use of binder yarns and waterblocking tapes.

Features and Benefits

Binderless* FastAccess® Technology

Innovative cable design that reduces cable access time up to 70 percent and lowers the risk of inadvertent fiber damage

Improved cable and fiber density

Small cable OD enables higher density and lower deployment cost; up to 96 fibers in 8 mm ID duct and up to 144 fibers in 10 mm ID duct

Optimized for air-assisted install in microducts


Capable of installation distances greater than 2000 m (6560 ft) at speeds up to 150 m/min (490 ft/min)

Mid-span express buffer tube performance


Meets the Telcordia GR-20 and RDUP/RUS PE-90 requirements for mid-span express buffer tube storage

Fully waterblocked loose tube, gel-filled design

Meets industry standard waterblocking requirements for outdoor cable



MiniXtend® Cable with Binderless* FastAccess® Technology, 72 F, SMF-28® Ultra fiber, Single-mode (G.652.D/G.657.A1)



MiniXtend® Cable with Binderless* FastAccess® Technology, 72 F, SMF-28® Ultra fiber, Single-mode (G.652.D/G.657.A1)

MiniXtend® Cable with Binderless* FastAccess® Technology 72 F, SMF-28® Ultra fiber, Single-mode (G.652.D/G.657.A1)

CORNING

Specifications

General Specifications

Installation Methods	Microduct
Outer Jacket Print	Feet
Cable Type	Stranded Loose Tube
Environment	Outdoor
Product Type	Dielectric
Fiber Category	SMF-28® Ultra
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Common Installations	Outdoor microduct, indoor when installed according to National Electrical Code® (NEC®) Article 770
Design and Test Criteria	IEC 60794-5-10
Corning Recommendations	This cable should be placed in microduct for all applications, including aerial.

Environmental Conditions

Temperature Range, Installation	-15 °C to 60 °C (5 °F to 140 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Central Element	Dielectric
Fiber Count	72
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)
Buffer Tube Color	Blue, Orange, Green, Brown, Slate, White

MiniXtend® Cable with Binderless* FastAccess® Technology 72 F, SMF-28® Ultra fiber, Single-mode (G.652.D/G.657.A1)

CORNING

Cable Design

Buffer Tube Diameter	1.4 mm (0.06 in)
Number of Active Tubes	6
Number of Tube Positions	6
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Color Code Standards	Telcordia

Mechanical Specifications

Max. Tensile Strength, Short-Term	890 N (200.08 lbf)
Nominal Outer Diameter	5.4 mm (0.21 in)
Min. Bend Diameter Installation	216 mm (8.5 in)
Min. Bend Diameter Operation	164 mm (6.46 in)
Min. Duct Size Diameter	8 mm (0.31 in)
Optimal Duct Size	10 mm (0.39 in)

Optical Characteristics

Fiber Code	Z
Performance Option Code	22
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.34 dB/km / 0.34 dB/km / 0.22 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1

Dimensions

Cable Weight	23 kg/km (15.46 lb/1000 ft)
--------------	-----------------------------

MiniXtend® Cable with Binderless* FastAccess® Technology 72 F, SMF-28® Ultra fiber, Single-mode (G.652.D/G.657.A1)

The Corning logo is a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.