

SST-Ribbon Single-Tube, Gel-Free, Armored Cable 144 F, Bend-improved Single-mode (OS2)



Part Number:
144ZC5-14100D53

Corning SST-Ribbon cables represent a truly innovative breakthrough in outside plant cable technology. Providing up to 216 fibers in a compact design, the enhanced coupling features ensure the ribbon stack and cable act as one unit, providing long-term reliability in aerial, duct and direct-buried applications. These features also minimize ribbon movement in situations where cable vibration may occur. The cable consists of a single buffer tube containing a stack of up to 18 12-fiber ribbons wrapped within a water-swellable foam tape and surrounded by a second water-swellable tape. Steel strength members located 180 degrees apart under the cable jacket provide tensile and anti-buckling strength. Armored cables include a copolymer-coated corrugated steel tape armor layer. The cable is jacketed with a black UV-resistant polyethylene sheath. The 12-fiber ribbons have readily identifiable ribbon IDs and fiber colors and geometries that result in excellent mass-splicing yields.

Features and Benefits

Gel-free waterblocking technology

Craft-friendly cable preparation

Innovative waterblocking technology


Prevents water penetration

12-fiber ribbons with ribbon IDs


Easy identification

Up to 216 fibers in a compact design

Easily fits in 1.0 inch inner diameter duct



SST-Ribbon Single-Tube, Gel-Free, Armored Cable, 144 F, Bend-improved Single-mode (OS2)



SST-Ribbon Single-Tube, Gel-Free, Armored Cable, 144 F, Bend-improved Single-mode (OS2)

SST-Ribbon Single-Tube, Gel-Free, Armored Cable 144 F, Bend-improved Single-mode (OS2)

CORNING

Specifications

General Specifications	
Cable Type	Ribbon
Environment	Outdoor
Product Type	Dielectric armor
Fiber Category	SMF-28® Ultra fiber
Application	Aerial, Duct, Direct Buried
Cable geometry	Round

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Common Installations	Outdoor lashed aerial, duct and direct-buried, indoor when installed according to National Electrical Code® (NEC®) Article 770
Design and Test Criteria	ANSI/ICEA S-87-640, Telcordia GR-20, RDUP PE-90

Environmental Conditions	
Temperature Range, Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design	
Buffer Tube Color	Natural
Fiber Count	144
Buffer Tube Diameter	7.8 mm (0.31 in)
Number of Ripcords	2
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Outer Jacket Color	Black

SST-Ribbon Single-Tube, Gel-Free, Armored Cable 144 F, Bend-improved Single-mode (OS2)

CORNING

Cable Design

Outer Jacket Material	Polyethylene (PE)
Tensile Strength Elements and/or Armoring - Layer 1	Steel strength members
Tape	Water-swellable
Tape, Layer 1	Water-swellable
Tape, Layer 2	Water-swellable
Ribbons per Tube	12
Fibers per Ribbon	12

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Nominal Outer Diameter	13.9 mm (0.55 in)
Min. Bend Diameter Operation	278 mm (10.94 in)
Min. Bend Diameter Installation	418 mm (16.46 in)

Optical Characteristics

Fiber Code	Z
Fiber Name	SMF-28® Ultra fiber
Fiber Type	Single-mode
Performance Option Code	00
Maximum Attenuation	0.35 dB/km / 0.35 dB/km / 0.25 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Category	G.652.D/G.657.A1

Dimensions

Cable Weight	187 kg/km (125.66 lb/1000 ft)
Length	0 mm (0 in)

SST-Ribbon Single-Tube, Gel-Free, Armored Cable 144 F, Bend-improved Single-mode (OS2)

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm