

2178 Splice Closure S/LS/LL/SL 2178-LS/FR, BEAD-BABA

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Part Number:
2178-LS-FR-A2-NN-2-US

A full line of closures and accessories designed to protect fiber optic facilities. The Fiber Optic Splice Closure 2178 family has earned its reputation for reliable protection of fiber optic facilities. Now, the 2178 family includes many models and configurations for more flexibility to help meet the complex needs of today's fiber optic networks.

Providing excellent system flexibility for both existing and new fiber deployments, the 2178 closure saves you time and money, while the smart design makes your job easier, offering reusable gaskets to make re-entry easy with almost no training necessary. The various sizes, cable addition kits and multiple grommets make system expansion even easier and the flexible tray systems allow for positional or fixed splice inserts. Suitable for all cable types but optimized for Ribbon cables, the 2178 closure will support any application.

The 2178 family includes seven distinct models – XSB, XLB, S, SL, LS, LL, and XL in flame retardant and non-flame-retardant versions with flexibility built-in for growing networks.

2178 Splice Closure S/LS/LL/SL 2178-LS/FR, BEAD-BABA

CORNING

Specifications

General Specifications

Cable Type	Branch, Express
Product Type	Splice Closure

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Compliance	BEAD-BABA

Design

Closure Type	Bolted Half
Sealing Type	Watertight

Dimensions

Height	215.9 mm (8.5 in)
Width	233.7 mm (9.2 in)
Depth	556.3 mm (21.9 in)

Ordering Information

Product Number	2178-LS-FR-A2-NN-2-US
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.