

Evolv® Terminal with Pushlok® Technology 2 port, stubbed, SST Toneable, 10 ft

CORNING

Part Number:
DMA2F1TDD1NC010F0P

Pushlok® hardened connector technology is the key component enabling smaller terminals for FTTx networks than ever before. Designed for use in nearly every access network environment, the terminal is small enough to be placed in existing handholes or pedestals where space is paramount, on building facades, or in aerial networks (pole- or strand-mount). Improved aesthetics improve end-user adoption for facade applications. There are two styles of terminals designed to meet various space and density requirements: terminals with one row of adapter ports and terminals with two rows of adapter ports. For terminals with one row of adapter ports, the ports are aligned in a single row with the input stub on the left and 2-, 4-, 6- or 8-distribution ports on the right. For terminals with two rows of ports, the input stub is on the front left of the terminal and there are 6-, 8-, 12- or 16- distribution ports. Each port's corresponding release button is actuated to remove the dust cap or drop. When installing drops, the keyed ports provide an audible and physical positive feedback minimizing technician variation and potential damage due to mishandling.

Features and Benefits

Pushlok™ cable assembly connector ports for customer drop terminations

Lower installation cost and increased speed of connection

Standard and integrated splitter terminal options

Durability

Solution supports various architecture types

Durability

100 lb cable tensile strength

Available stubbed or preterminated with OptiTip® multifiber connector technology

Compatible with existing FlexNAP™ installations

Small form factor optimizes space in pedestals/handholes


Lower profile overall with drop entry ports on bottom

Ultrasonically welded housing

Eliminates water ingress potential and prevents unwanted entry in the field

Factory-terminated polished connectors

Eliminates loss associated with excess fusion splices



Evolv® Terminal with Pushlok® Technology, 2 port, stubbed, SST Toneable, 10 ft

Evolv® Terminal with Pushlok® Technology 2 port, stubbed, SST Toneable, 10 ft



Specifications

| General Specifications | |
|-------------------------------------|----------------------------------------------------------|
| Product Type | Terminals |
| Environment | Outdoor |
| Cable Type | SST Flat Toneable Drop |
| Fiber Category | ITU-TG.652.D (OS2) |
| Packaging | Individual Pack |
| Preconnectorized "Stubbed" Hardware | No |
| Lockable | No |
| Cable type stubbed | SST Drop Cable |
| Mounting Type | Strand mount, Pole-mount, Pedestal mount, Handhole Mount |
| Splice option | No |
| Application | FTTx |
| Technology | Pushlok® |

| Standards | |
|--------------------------|-----------------------------------------------------------|
| RoHS | Free of hazardous substances according to RoHS 2011/65/EU |
| Design and Test Criteria | IP68 |

| Environmental Conditions | |
|------------------------------|-------------------------------------|
| Temperature Range, Operation | -40 °C to 85 °C (-40 °F to 185 °F) |
| Temperature Range, Storage | -40 °C to 85 °C (-40 °F to 185 °F) |

| Design | |
|-------------------|---|
| Fiber Count | 2 |
| Input Fiber Count | 2 |
| Fibers per Port | 1 |

Evolv® Terminal with Pushlok® Technology 2 port, stubbed, SST Toneable, 10 ft

CORNING

Design

| | |
|------------------------------------------------|------------------------|
| Number of single-fiber ports, SC APC connector | 2 |
| Housing Material | Plastic |
| Pigtail Length | 10 ft |
| Input Cable Type | SST Flat Toneable Drop |
| Locking Availability | No |
| Sealing Type | Welded |
| Housing Color | Black |
| Number of Fibers in Input Cable | 2 |
| Number of Ports | 2 |

Design - Adapter

| | |
|--------------|----------|
| Adapter Type | Pushlok® |
|--------------|----------|

Mechanical Specifications

| | |
|------------------|-----------------|
| Cold Mate/Demate | -40 °C (-40 °F) |
| Cable Length | 10 ft |

Optical Specification - Hardware

| | |
|----------------------------|--------|
| Module Insertion Loss, Max | 0.5 dB |
| Reflectance, Maximum | 65 dB |

Connector Specs

| | |
|------------------|---------|
| Polish | APC |
| Housing Color | Black |
| Housing Material | Plastic |

Evolv® Terminal with Pushlok® Technology 2 port, stubbed, SST Toneable, 10 ft

CORNING

Specifications - Connector A

| | |
|-------------------------|-----------|
| Connector Type | Pushlok® |
| Housing Color | Black |
| Polish | APC |
| Housing Material | Plastic |
| Endface Type | APC |
| Insertion Loss, Max. | 0.5 dB |
| Reflectance | > 65 dB |
| Insertion Loss, Typical | ≤ 0.15 dB |

Dimensions

| | |
|--------|------------------|
| Length | 10 ft |
| Height | 30 mm (1.18 in) |
| Width | 84 mm (3.31 in) |
| Depth | 152 mm (5.98 in) |
| Weight | 0.45 kg |

Ordering Information

| | |
|--------------------|--------------------|
| Product Number | DMA2F1TDD1NC010F0P |
| Packaging Method | Box |
| Shipping Weight | 0.45 kg |
| Units per Delivery | 1/1 |
| Shipping Height | 762 mm (30 in) |
| Shipping Width | 762 mm (30 in) |
| Shipping Depth | 152 mm (5.98 in) |



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm